


Omlijsting voor uitsparingen voorpaneel FMC Mezzanine, VITA 57,1



CATALOGUSNUMMER

20835-849

Een FMC-omlijsting is aangebracht in de uitsparingen van het voorpaneel van de FMC-tussenverdieping, set van 10 FMC-bezels.

KENMERKEN

De FMC-omlijsting is aangebracht in de uitsparingen van het voorpaneel van de FMC-tussenverdieping

FMC-afdekking kan optioneel worden afgeschermd met geleidende O-ring. Bestel deze apart

Materiaal, al-extrusie (geanodiseerd, oppervlaktegeleidend)



PRODUCTKENMERKEN

Producttype: Frontpaneel

Type: Mezzanine-frontpaneel

Type accessoire: Frontpaneel

Montage: Vastgeklikt

EMC-afscherming: Nee (achteraf te monteren)

Type pakking: O-ring EMC

Materiaal: Aluminium

Afwerking voorzijde: Geanodiseerd

Afwerking achterzijde: Geleidend

Behandelde randen: Nee

Hoogte: 58.45mm

Breedte: 12.8mm

Diepte: 2.5mm

Voldoet aan: FMC Mezzanine; IEEE P1386

Hoeveelheid in verpakking: 10

Nettogewicht: 0.1kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AANVULLENDE PRODUCTGEGEVENS

Bestel EMC O-ringpakking afzonderlijk.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

