

Rack Safety Plus, 3 u, 400 V AC, 63 A, CEE

CATALOGUSNUMMER

21270-063



De nVent SCHROFF Rack Safety Plus-unit is een 19-inch stroomverdelingseenheid die wordt gebruikt om elektrische of elektronische apparaten als centrale stroomschakelaar van wisselstroom te voorzien. Daarnaast is het uitgerust met een noodstopfunctie.

KENMERKEN

19", 4 u voedingseenheid met noodstopfunctie

Levert netvoeding aan elektrische of elektronische apparaten als centrale stroomschakelaar

230 / 400 V 3-fasig, 63 A netingang met netstroomonderbreker

AC-uitgangen met verschillende typen connectoren, geschakeld met een AAN/UIT-schakelaar

Permanente AC-uitgangen (service)

Alle uitgangen worden beschermd door stroomonderbrekers

De noodstopfunctie voldoet aan de eisen van en 60947-5-1 en en 60204-1 en is vandalismebestendig

Er kan een extra externe noodstopknop op het systeem worden aangesloten

PRODUCTKENMERKEN

Producttype: Stroomverdeler

Type accessoire: Accessoires voor stroomverdeling

Afdekking van de stroomonderbreker: Ja

EMC-filter: Nee

Functie: Noodstop

Ingangsspanning AC: 400V

Inschakelstroombegrenzer: Nee

Aantal fasen: 3

Rekhoogte: 4U

Aardlekschakelaar: Ja

Type fitting: CEE; IEC C13

Overspanningsbeveiliging: Nee

Werkt met: Varistar; Varistar CP; Novastar

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail

price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AANVULLENDE PRODUCTGEGEVENS

Raadpleeg voor de exacte configuratie van optionele functies en voorbeeldconfiguratie de tabel met geleverde items(s).

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

