



		"B" can be simplified		"B" simplification not recommended	
light = 1	light = 1	-	+	+	+
	light = 2	+	notch 1/2 flange (B) recommended	notch 1/2 flange and notch 1/2 flange not recommended	+
light = 2	light = 1	+	+	-	-
	light = 2	notch 1/2 flange	notch 1/2 flange		
light = 3	light = 1				
	light = 2				
light = 4	light = 1				
	light = 2				
light = 5	light = 1				
	light = 2				
light = 6	light = 1				
	light = 2				
light = 7	light = 1				
	light = 2				
light = 8	light = 1				
	light = 2				
light = 9	light = 1				
	light = 2				
light = 10	light = 1				
	light = 2				
light = 11	light = 1				
	light = 2				
light = 12	light = 1				
	light = 2				
light = 13	light = 1				
	light = 2				
light = 14	light = 1				
	light = 2				
light = 15	light = 1				
	light = 2				
light = 16	light = 1				
	light = 2				
light = 17	light = 1				
	light = 2				
light = 18	light = 1				
	light = 2				
light = 19	light = 1				
	light = 2				
light = 20	light = 1				
	light = 2				
light = 21	light = 1				
	light = 2				
light = 22	light = 1				
	light = 2				
light = 23	light = 1				
	light = 2				
light = 24	light = 1				
	light = 2				
light = 25	light = 1				
	light = 2				
light = 26	light = 1				
	light = 2				
light = 27	light = 1				
	light = 2				
light = 28	light = 1				
	light = 2				
light = 29	light = 1				
	light = 2				
light = 30	light = 1				
	light = 2				
light = 31	light = 1				
	light = 2				
light = 32	light = 1				
	light = 2				
light = 33	light = 1				
	light = 2				
light = 34	light = 1				
	light = 2				
light = 35	light = 1				
	light = 2				
light = 36	light = 1				
	light = 2				
light = 37	light = 1				
	light = 2				
light = 38	light = 1				
	light = 2				
light = 39	light = 1				
	light = 2				
light = 40	light = 1				
	light = 2				
light = 41	light = 1				
	light = 2				
light = 42	light = 1				
	light = 2				
light = 43	light = 1				
	light = 2				
light = 44	light = 1				
	light = 2				
light = 45	light = 1				
	light = 2				
light = 46	light = 1				

34566-763

KENMERKEN

Aluminium extrusie, geanodiseerde afwerking, geleidend
contactoppervlak



Werkt met: Subracks

AANVULLENDE PRODUCTGEGEVENS

nVent.com/SCHROFF | 1

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

