

WBT Performance kabellade preform-T



The nVent CADDY Wire Basket Tray PreForm Tee is a precision-engineered solution designed to streamline cable tray installations when routing cabling in two or three different directions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Tee delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Tee significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

KENMERKEN

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in two or three directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Materiaal: Staal
Afwerking: Voorgegalvaniseerd;Polyurethaan



SPECIFICATIES

Table 1/2

Catalogusnummer	Kleur	Hoogte (H)	Breedte (W)	Lengte (L)	Gatgrootte (HS)	Radius (R)	Gewicht eenheid
WBTT2X12		50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64mm	2.722 kg
WBTT2X12BA	Zwart	50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64mm	2.722 kg
WBTT2X18		50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64mm	4.536 kg
WBTT2X18BA	Zwart	50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64mm	4.536 kg

Catalogusnummer	Kleur	Hoogte (H)	Breedte (W)	Lengte (L)	Gatgrootte (HS)	Radius (R)	Gewicht eenheid
WBTT2X24		50.8 mm	817.88 mm	1013.46m m	19.05 mm	94.64mm	7.257 kg
WBTT2X24BA	Zwart	50.8 mm	817.88 mm	1013.46m m	19.05 mm	94.64mm	7.257 kg
WBTT2X4		50.8 mm	317.5 mm	513.08mm		94.64mm	0.454 kg
WBTT2X4BA	Zwart	50.8 mm	317.5 mm	513.08mm		94.64mm	0.454 kg
WBTT2X6		50.8 mm	365.76 mm	561.34mm		94.64mm	1.361 kg
WBTT2X6BA	Zwart	50.8 mm	365.76 mm	561.34mm		94.64mm	1.361 kg
WBTT2X8		50.8 mm	416.56 mm	612.14mm		94.64mm	1.814 kg
WBTT2X8BA	Zwart	50.8 mm	416.56 mm	612.14mm		94.64mm	1.814 kg
WBTT6X6		152.39999999999998 mm					
WBTT2X4S4		50.8 mm					
WBTT4X12		101.6 mm					
WBTT4X12BA	Zwart	101.6 mm					
WBTT4X18		101.6 mm					
WBTT4X18BA	Zwart	101.6 mm					
WBTT4X24		101.6 mm					
WBTT4X24BA	Zwart	101.6 mm					

Table 2/2

Catalogusnummer	Kleur	Hoogte (H)	Breedte (W)	Lengte (L)	Gatgrootte (HS)	Radius (R)	Gewicht eenheid
WBTT4X4		101.6 mm					
WBTT4X4BA	Zwart	101.6 mm					
WBTT4X6		101.6 mm					
WBTT4X6BA	Zwart	101.6 mm					
WBTT6X12		152.4 mm					
WBTT6X12BA	Zwart	152.4 mm					
WBTT6X18		152.4 mm					
WBTT6X18BA	Zwart	152.4 mm					
WBTT6X24		152.4 mm					
WBTT6X24BA	Zwart	152.4 mm					
WBTT6X36		152.4 mm					

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

Noord-Amerika

+1.800.753.9221
optie 1 – Klantenservice
optie 2 – Technische
ondersteuning

Europa

Nederland:
+31 800-0200135
Frankrijk:
+33 800 901 793

Europa

Duitsland:
800 1890272
andere landen:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

