

Kraagschroef, geribbelde kop, korte versie



Integrated load spreading, replaces separate washer.
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

KENMERKEN

Kraagschroef, geribbelde kop, korte versie

For EuropacPRO and RatiopacPRO

Knurled head for manual screwing / unscrewing

Producttype: Schroef
Type: Schroef
Werkt met: Frontpanelen



SPECIFICATIES

Table 1/2

Catalogusnummer	Lengte	Materiaal	Afwerking	Hoeveelheid in verpakking	Schroefdraadmaat	Diepte
21101-749	12.3mm	Messing	Vernikkeld	100	M2.5	18.3mm
21100-268	11mm	Messing	Vernikkeld	100	M2.5	
21101-106	11mm	Staal			M2.5	

Table 2/2

Catalogusnummer	Hoogte	Breedte	Schroefdraadlengte	Aanhaalmoment	Certificeringen
21101-749	8mm	8mm	12.3mm	0.3N·m	RoHS
21100-268				0.22N·m	
21101-106				0.22N·m	

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

