

Snapp-lukk-kanal/rør klemmer, S301, 7 mm Hull, Vanlig

KATALOGNUMMER

12MS1



The nVent CADDY Snap Close Conduit Clamps (M-Series) are a fast and efficient method to secure conduit branch circuits for electrical installations. The M-Series is designed to provide positional consistency in application by eliminating conduit offset as well as maintain spacing entering electrical boxes. Increase installation efficiency by utilizing our comprehensive conduit range for your next electrical project.

FUNKSJONER

Kan brukes for enten vertikale eller horisontale installasjoner

Fjerner behovet for sideforskyvning av kabelrør

Fingerlukking – verktøy er ikke nødvendig

Locking design has greater resistance to twisting loads and is stronger than any on the market

Low profile locking tabs and smooth gripping dimples remove the possibility of scrapes

812M and 16M feature double tabs to center conduit, increase range and holding power and prevent conduit from sliding

PRODUKTEGENSKAPER

Artikkelnummer: 179910

Materiale: Rustfritt stål 301 (EN 1.4310)



Ytre diameter (OD): 22 - 30 mm

Hullstørrelse (HS): 7 mm

Hulltype: Standard

Statisk belastning 1 (F1): 440N

Statisk belastning 2 (F2): 110N



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

Nord-Amerika

+1.800.753.9221

Alternativ 1 –

Kundeservice

Alternativ 2 – Teknisk

støtte

Europa

Nederland:

+31 800-0200135

Frankrike:

+33 800 901 793

Europa

Tyskland:

800 1890272

Andre land:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

