

Cat HP J-Hook Mod klips for M4–M12 gjengestang, 4,8 - 6,4mm tråd



KATALOGNUMMER

CATHPM4Z34

Improved nVent CADDY Cat HP Mod Clip J-Hook with Rod/Wire Clip allows for quick attachment to threaded rod or wire without screws or special tools. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

FUNKSJONER

Montering uten verktøy

Works with nVent J-Hook Versa-Mount technology from nVent CADDY



PRODUKTEGENSKAPER

Artikkelnummer: 186082


Overflate: NVent CADDY-armering

Materiale: Fjærstål

Stangstørrelse (RS): M4;M6;M8;M10;M12

Størrelse på kabel: 4.8 - 6.4 mm

Statisk belastning: 130N



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

Nord-Amerika

+1.800.753.9221

Alternativ 1 –

Kundeservice

Alternativ 2 – Teknisk

støtte

Europa

Nederland:

+31 800-0200135

Frankrike:

+33 800 901 793

Europa

Tyskland:

800 1890272

Andre land:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

