

Improved nVent CADDY Cat HP J-Hook with Multi-Function Clip



The Improved nVent CADDY Cat HP J-Hook with Multi-Function Clip is an innovative assembly featuring a combination of the Improved nVent CADDY Cat HP J-Hook with a Multi-Function Clip attachment. The Assembly simplifies cable management by offering quick attachment to threaded rod or wire without the need for screws or special tools.

Engineered for high-performance data cable management, this system supports Cat 5e, Cat 6, Cat 6A, Cat 7, and fiber optic cables with superior fill capacity and load ratings compared to most non-continuous alternatives. The Assemblies' rounded edges ensure proper bend radius support, protecting cable integrity and optimizing performance.

FUNKSJONER

Fully adjustable and easy to relocate to accommodate changes once installed

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



SPESIFIKASJONER

Table 1/2

Katalognummer	Artikkelnummer	Materiale	Overflate	Diameter	Område	Kabelkapasitet, kategori 5e
CAT16HP4Z34	181217	Stål, Spring Stål	Forhåndsgalvanisert, NVent CADDY-armering	25 mm	690mm ²	20

Katalognummer	Artikkelnummer	Materiale	Overflate	Diameter	Område	Kabelkapasitet, kategori 5e
CAT21HP4Z34	181258	Stål, Spring Stål	Forhåndsgalvanisert, NVent CADDY-armering	33.3 mm	1174m m ²	50
CAT32HP4Z34	181218	Stål, Spring Stål	Forhåndsgalvanisert, NVent CADDY-armering	50 mm	2561m m ²	90

Table 2/2						
Katalognummer	Artikkelnummer	Kabelkapasitet, kategori 6	Kabelkapasitet, kategori 6A	Størrelse på kabel	Stangstørrelse	Statisk belastning
CAT16HP4Z34	181217	15	10	3.9 - 4.8 mm ²	4, 6, 8, 10	130N
CAT21HP4Z34	181258	40	25	3.9 - 4.8 mm ²	4, 6, 8, 10	130N
CAT32HP4Z34	181218	60	35	3.9 - 4.8 mm ²	4, 6, 8, 10	130N

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

Nord-Amerika

+1.800.753.9221
Alternativ 1 –
Kundeservice
Alternativ 2 – Teknisk
støtte

Europa

Nederland:
+31 800-0200135
Frankrike:
+33 800 901 793

Europa

Tyskland:
800 1890272
Andre land:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

