

Wire Basket Tray Bar Splice



The nVent CADDY Wire Basket Tray Bar Splice offers a versatile solution for straight sections and fittings within shaped wire basket tray systems. Engineered for structural continuity, the Bar Splice delivers enhanced support between tray runs. With a slotted design, contractors can create innovative field configurations—ideal for forming reducers or achieving precise angles. Whether you're adapting tray geometry or reinforcing connections, the Bar Splice ensures a clean, secure fit with finishes that match your installation.

FUNKSJONER

Multiple color options to coordinate with cable tray selection

Creates additional support for cable tray runs

Optimal for angles 30 degrees and smaller


Materiale: Stål
Overflate: Elektrogalvanisert



SPESIFIKASJONER

Katalognummer	Farge	Høyde (H)	Bredde (W)	Lengde (L)	Enhetsvekt	Sertifiseringer
WBTBSPLICE		17.46 mm	4.55 mm	304.8mm	0.127 kg	
WBTBSPLICEBA	Svart	17.46 mm	4.55 mm	304.8mm	0.127 kg	
WBTBSPLICEKIT		17.46 mm	4.55 mm	304.8mm	0.127 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBTBSPLICEKITBA	Svart	17.46 mm	4.55 mm	304.8mm	0.127 kg	CE, nVent CADDY Wire Basket Tray System, UL

DIAGRAMMER



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

Nord-Amerika

+1.800.753.9221

Alternativ 1 –

Kundeservice

Alternativ 2 – Teknisk

støtte

Europa

Nederland:

+31 800-0200135

Frankrike:

+33 800 901 793

Europa

Tyskland:

800 1890272

Andre land:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

