


# Wire Basket Tray PreForm Elbow 90°



The nVent CADDY Wire Basket Tray PreForm Elbow 90° is a precision-engineered solution designed to streamline cable tray installations when a directional change is needed. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Elbow 90° delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Elbow 90° significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

## FUNKSJONER

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

**Materiale:** Stål  
**Overflate:** Forhåndsgalvanisert;Polyuretan



## SPESIFIKASJONER

Table 1/2


| Katalognummer | Farge | Høyde (H) | Bredde (W) | Lengde (L) | Hullstørrelse (HS) | Radius (R) |
|---------------|-------|-----------|------------|------------|--------------------|------------|
| WBTR902X12    |       | 50.8 mm   | 515.62 mm  | 515.62mm   | 19.05 mm           | 94.64mm    |
| WBTR902X12BA  | Svart | 50.8 mm   | 515.62 mm  | 515.62mm   | 19.05 mm           | 94.64mm    |
| WBTR902X18    |       | 50.8 mm   | 665.734 mm | 665.734mm  | 19.05 mm           | 94.64mm    |
| WBTR902X18BA  | Svart | 50.8 mm   | 665.734 mm | 665.734mm  | 19.05 mm           | 94.64mm    |
| WBTR902X24    |       | 50.8 mm   | 817.88 mm  | 817.88mm   | 19.05 mm           | 94.64mm    |
| WBTR902X24BA  | Svart | 50.8 mm   | 817.88 mm  | 817.88mm   | 19.05 mm           | 94.64mm    |
| WBTR902X4     |       | 50.8 mm   | 317.7 mm   | 317.7mm    |                    | 94.64mm    |
| WBTR902X4BA   | Svart | 50.8 mm   | 317.7 mm   | 317.7mm    |                    | 94.64mm    |
| WBTR902X6     |       | 50.8 mm   | 365.76 mm  | 365.76mm   |                    | 94.64mm    |

| Katalognummer | Farge | Høyde (H) | Bredde (W) | Lengde (L) | Hullstørrelse (HS) | Radius (R) |
|---------------|-------|-----------|------------|------------|--------------------|------------|
| WBTR902X6BA   | Svart | 50.8 mm   | 365.76 mm  | 365.76mm   |                    | 94.64mm    |
| WBTR902X8     |       | 50.8 mm   | 416.56 mm  | 416.56mm   |                    | 94.64mm    |
| WBTR902X8BA   | Svart | 50.8 mm   | 416.56 mm  | 416.56mm   |                    | 94.64mm    |

Table 2/2

| Katalognummer | Enhetsvekt | Sertifiseringer                                  |
|---------------|------------|--------------------------------------------------|
| WBTR902X12    | 1.814 kg   | cUL, UL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X12BA  | 1.814 kg   | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X18    | 3.175 kg   | CE, nVent CADDY Wire Basket Tray System, cUL, UL |
| WBTR902X18BA  | 3.175 kg   | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X24    | 4.99 kg    | cUL, UL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X24BA  | 4.99 kg    | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X4     | 0.454 kg   | UL, CE, nVent CADDY Wire Basket Tray System, cUL |
| WBTR902X4BA   | 0.454 kg   | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X6     | 0.907 kg   | CE, nVent CADDY Wire Basket Tray System, cUL, UL |
| WBTR902X6BA   | 0.907 kg   | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X8     | 0.907 kg   | UL, cUL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X8BA   | 0.907 kg   | CE, nVent CADDY Wire Basket Tray System          |

## DIAGRAMMER



## ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieill. Instruksjonsark er tilgjengelig på [www.nvent.com](http://www.nvent.com) og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

#### **Nord-Amerika**

+1.800.753.9221

Alternativ 1 –

Kundeservice

Alternativ 2 – Teknisk

støtte

#### **Europa**

Nederland:

+31 800-0200135

Frankrike:

+33 800 901 793

#### **Europa**

Tyskland:

800 1890272

Andre land:

+31 13 5835404

#### **APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. Alle nVent-merker og -logoer er eid eller lisensiert av nVent Services GmbH eller dets datterselskaper. Alle andre varemerker eies av de respektive eierne. nVent forbeholder seg retten til å endre spesifikasjonene uten forvarsel.

Dette dokumentet er systemgenerert.

