

WBT-kabelbrett for preform-T-skjorte



The nVent CADDY Wire Basket Tray PreForm Tee is a precision-engineered solution designed to streamline cable tray installations when routing cabling in two or three different directions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Tee delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Tee significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

FUNKSJONER

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in two or three directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Materiale: Stål
Overflate: Forhåndsgalvanisert;Polyuretan



SPESIFIKASJONER

Table 1/2

Katalognummer	Farge	Høyde (H)	Bredde (W)	Lengde (L)	Hullstørrelse (HS)	Radius (R)	Enhetsvekt
WBTT2X12		50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64mm	2.722 kg
WBTT2X12BA	Svart	50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64mm	2.722 kg
WBTT2X18		50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64mm	4.536 kg
WBTT2X18BA	Svart	50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64mm	4.536 kg

Katalognummer	Farge	Høyde (H)	Bredde(W)	Lengde (L)	Hullstørrelse (HS)	Radius(R)	Enhetsvekt
WBTT2X24		50.8 mm	817.88 mm	1013.46m m	19.05 mm	94.64mm	7.257 kg
WBTT2X24BA	Svart	50.8 mm	817.88 mm	1013.46m m	19.05 mm	94.64mm	7.257 kg
WBTT2X4		50.8 mm	317.5 mm	513.08mm		94.64mm	0.454 kg
WBTT2X4BA	Svart	50.8 mm	317.5 mm	513.08mm		94.64mm	0.454 kg
WBTT2X6		50.8 mm	365.76 mm	561.34mm		94.64mm	1.361 kg
WBTT2X6BA	Svart	50.8 mm	365.76 mm	561.34mm		94.64mm	1.361 kg
WBTT2X8		50.8 mm	416.56 mm	612.14mm		94.64mm	1.814 kg
WBTT2X8BA	Svart	50.8 mm	416.56 mm	612.14mm		94.64mm	1.814 kg
WBTT6X6		152.39999999999998 mm					
WBTT2X4S4		50.8 mm					
WBTT4X12		101.6 mm					
WBTT4X12BA	Svart	101.6 mm					
WBTT4X18		101.6 mm					
WBTT4X18BA	Svart	101.6 mm					
WBTT4X24		101.6 mm					
WBTT4X24BA	Svart	101.6 mm					

Table 2/2

Katalognummer	Farge	Høyde (H)	Bredde (W)	Lengde (L)	Hullstørrelse (HS)	Radius (R)	Enhetsvekt
WBTT4X4		101.6 mm					
WBTT4X4BA	Svart	101.6 mm					
WBTT4X6		101.6 mm					
WBTT4X6BA	Svart	101.6 mm					
WBTT6X12		152.4 mm					
WBTT6X12BA	Svart	152.4 mm					
WBTT6X18		152.4 mm					
WBTT6X18BA	Svart	152.4 mm					
WBTT6X24		152.4 mm					
WBTT6X24BA	Svart	152.4 mm					
WBTT6X36		152.4 mm					

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

Nord-Amerika

+1.800.753.9221

Alternativ 1 –

Kundeservice

Alternativ 2 – Teknisk

støtte

Europa

Nederland:

+31 800-0200135

Frankrike:

+33 800 901 793

Europa

Tyskland:

800 1890272

Andre land:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

