

T-kontakt

FUNKSJONER

For 90° lederkoblinger



SPESIFIKASJONER

Table 1/2



Katalognummer	Artikkelnummer	Materiale	Lederstørrelse	Dybde (D)	Høyde (H)	Bredde (W)
CTR8CU	710030	Messing	8 mm fast, 10 mm fast	21mm	46 mm	40 mm

Table 2/2

Katalognummer	Artikkelnummer	nVent ERICO Cu-Bond-leder	Enhetsvekt	Samsvarer med
CTR8CU	710030	CBSC10	0.17 kg	IEC® 62561-1

YTTERLIGERE PRODUKTDETALJER

IEC-overholdelse er kun gyldig for oppførte nVent ERICO Cu-Bond ledere.



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

Nord-Amerika

+1.800.753.9221

Alternativ 1 –

Kundeservice

Alternativ 2 – Teknisk

støtte

Europa

Nederland:

+31 800-0200135

Frankrike:

+33 800 901 793

Europa

Tyskland:

800 1890272

Andre land:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

