


Veggmonteringsbraketter Heavy Duty, AWHD



Mounting brackets for hygienic wall fixing. Provides an space between the enclosure and the wall to facilitate cleaning operations. It includes the sealing washers to guarantee the IP rating. Machining required. Design according to EHEDG standards.

FUNKSJONER

Beskrivelse: Monteringsbraketter for hygienisk veggmontering. Sørger for et mellomrom mellom skapet og veggen, slik at det kan rengjøres der. Omfatter tetningsskiver for å garantere IP-klassifiseringen. Maskinell bearbeiding er nødvendig på rustfritt stål. Design i henhold til EHEDG-standarder.

Materiale: AISI 304 rustfritt stål. Pakning i FDA godkjent silikon.

Pakning: 1 brakett med monteringstilbehør.

Materiale: Rustfritt stål 304

Overflate: Børstet

SPESIFIKASJONER

Katalognummer	E-nummer	Høyde	Bredde	Dybde	Produktserie	Kapslingsmateriale
AWHD050	2411010	32mm	32mm	50mm	Veggmontert	Rustfritt stål
AWHD300	2411011	32mm	32mm	300mm	Veggmontert	Rustfritt stål

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieill. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.