


Ramme for FMC Mezzanine frontpanel Cutouts, VITA 57,1



KATALOGNUMMER

20835-849

En FMC-ramme er montert i FMC mezzanine frontpanel utsparinger, sett med 10 FMC-rammer.

FUNKSJONER

FMC-rammen er montert i FMC mezzanin frontpanel utsparinger

FMC-deksel kan eventuelt skjermes med ledende O-ring, vennligst bestill dette separat

Materiale, Al-ekstrudering (anodisert, overflateledende)



PRODUKTEGENSKAPER

Produkttype: Frontpanel

Type: Mezzanine-frontpanel

Tilbehørstype: Frontpanel

Montering: Klikket på plass

EMC-beskyttelse: Nei (kan monteres etterpå)

Pakning: O-ring EMC

Materiale: Aluminium

Fremre overflate: Anodisert

Bakre flate: Strømledende

Behandlede kanter: Nei

Høyde: 58.45mm

Bredde: 12.8mm

Dybde: 2.5mm

Samsvarer med: FMC Mezzanine; IEEE P1386

Antall pakker: 10

Overflate: Anodisert

Nettovekt: 0.1kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

Bestill EMC O-ringpakning separat.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

