


Frontpanelsett, skjermet, bunnhengslet, 3 U, 42 HP, 2,5 mm, Al, fremre anodisert, ledende bak



KATALOGNUMMER

20848-599

U-profil, bunnhengslet frontpanel for tekstilpakning.

FUNKSJONER

U-profil frontpanel kan åpnes ved 135° (ikke RatiopacPRO) åpningsvinkel

Muliggjør montering på horisontale skinner

Skjermet, U frontpanel med tekstil EMC-pakning

Egnet for subrakker (EuropacPRO) og kofferter (RatiopacPRO, PropacPRO, CompacPRO)



PRODUKTEGENSKAPER

Rackhøyde: 3U

Tilbehørstype: Frontpanel

Rackbredde: 42HP

Antall pakker: 1

Montering: Hengslet, bunn

Pakning: Tekstil

Fremre overflate: Anodisert

Bakre flate: Strømledende

Behandlede kanter: Nei

Samsvarer med: IEC 60297-3-101; IEEE 1101,1/10

Dybde (D): 2.5mm

EMC-beskyttelse: Nei (kan monteres etterpå)

Overflate: Anodisert; Passivert

Høyde (H): 128.4mm

Materiale: Aluminium

Produkttype: Frontpanel

Bredde (W): 213mm

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

Frontpanelet kan fjernes i åpen posisjon ($> 135^\circ$).

Technical drawing of a rectangular plate with the following dimensions and features:

- Overall width: A
- Overall height: H
- Top left corner: 7.45 (horizontal) and 3 (vertical)
- Top edge: B (from left edge) and C (from right edge)
- Bottom left corner: 15.6 (horizontal) and 8.2 (vertical)
- Bottom edge: D (from left edge) and $B - 25.4$ (from right edge)
- Bottom right corner: 3 (horizontal) and 3.1 (vertical)
- Bottom right corner chamfer: $M2.5$
- Section X-X: Shows a cross-section with a width of 6.2 and a height of 2.5 .
- Section Y-Y: Shows a cross-section with a width of 6.2 and a height of 2.5 .

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Straubenhardt, Germany
 +49.7082.794.0
 Betschdorf, France
 +33.3.88.90.64.90
 Warsaw, Poland
 +48.22.209.98.35
 Assago, Italy
 +39.02.932.7141
 Chat with us:
nvent.com/schroff

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Dette dokumentet er systemgenerert.