

# Chassis-overvåkingsmodul CMM

Foreldet

## KATALOGNUMMER

23207-022

Overvåking av spenning, temperaturer og digitale innganger.


## FUNKSJONER

Databuss for kommunikasjon med SCHROFF Fan Control Module (FCM)

Pluggbar i 3 U Eurocard format

Innganger og utganger for VME- og CPCI-spesifikke signaler, ytterligere digitale og LED-utganger

Kommunikasjon og fjernkontroll via RS 232 eller Ethernet-grensesnitt (10BaseT)



| Status Monitor | Temp.             |
|----------------|-------------------|
| Voltage:       | CMM [23] °C       |
| +1.2V          | FCM [24] °C       |
| +5.0V          | Fan Speed         |
| +12.0V         | [61] %            |
| -12.0V         | Fan Speed Setting |
| Temperature    | T1 [25] °C        |
| CMM            | T2 [50] °C        |
| FCM            | Temp. Alarm       |
| Fan Speed      | CMM [40] °C       |
| Fan 1          | FCM [40] °C       |
| Fan 2          |                   |
| Fan 3          |                   |



## PRODUKTEGENSKAPER

Produkttype: Systemmodul

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

## ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelig på [www.nvent.com](http://www.nvent.com) og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

