


Airbender, Card Guide Insert, 70P blokkering, 4HP, 160mm, 10 stykker Kit

KATALOGNUMMER

24563-040



nVent SCHROFF Airbender-innlegg forbedrer kjøleeffektiviteten med opptil 85 % per spalte ved å balansere luftstrømmen i miljøer med blandet impedans. Det er enkelt å installere, reduserer viftestøy og forbedrer den generelle systemytelsen.

FUNKSJONER

Airbender-kortførerinnsetter forbedrer kjøleeffektiviteten i elektroniske systemer med opptil 85 % per 4HP-spor ved å balansere luftstrømmen i miljøer med blandet luftimpedans

70 % blokkering: Airbender introduserer ekstra luftimpedans i spalter med mindre kritiske komponenter, omdirigerer luftstrømmen til mer sårbare soner og sikrer bedre kjøleresultater for alle kort

Enkel installasjon: Du kan bare klemme Airbender inn i nVent SCHROFF plastkort og eventuelt feste den med en skrue

Favoriserer redusert støyutvikling fra viftene ved å opprettholde dem på et effektivt driftspunkt

Luftbender og kassettePRO kan ikke brukes sammen i samme spor.

PRODUKTEGENSKAPER

Produkttype: Luftskjerm

Produktserie: EuropacPRO; RatiopacPRO; RatiopacPRO Air; CompacPRO; PropacPRO; Inpac

Fungerer med: Delrack; Esker; Systemer

Rackbredde: 4HP

Dybde: 160mm

Materiale: Polykarbonat

Antall pakker: 10

Farge: Grå

Samsvarer med: EN 45545-2; UL® 94V-0

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

Airbenders med ulike blokkeringsnivåer tilgjengelig på forespørsel.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

