

High Thermal VITA conduction avkjølt Assemblies, 3UVPX48.2-PS260HTSI-311



KATALOGNUMMER

3UVPX48.2-PS260HTSI-311

Bestill og administrer ett delenummer for hele CCA-enheten, inkludert delmerking og komponentmerking, samt kortluker, ekstraktorer, kodingsnøkler, EMC-pakninger og varmeputer.

FUNKSJONER

Full design tjenester inkludert termisk analyse

Rask behandlingstid 3D-printede CCA-er og rammer for tilpasning

Nedlastbare standarder compatible CAD maler - 3 U og 6 U maler tilgjengelig

Tilgjengelig i svart anodise, kjemisk film, elektroløs nikkel finish

ESD-emballasje tilgjengelig



PRODUKTEGENSKAPER

Produkttype: Lederblokk

Fungerer med: Innkapslinger med ledekjøling

Klemmekraft: 272 – 318kgf

Mellomromsbredde: PCB + (7.0 - 7.9 mm)

Designfunksjon: Toleransekompensering

Termisk ytelse: Best

Profil: 6.35 x 6.26 mm

Rackhøyde: 3U

Materiale: Aluminium

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

Fra tid til annen kan nVent endre sine produktspesifikasjoner for å være i samsvar med gjeldende industri, militære eller andre relevante standarder. Med mindre annet er gjensidig skriftlig avtalt, kan kansellerte eller erstattede militære spesifikasjoner sertifiseres i henhold til de nyeste eller erstatter spesifikasjonene. Produkter som er produsert i samsvar med slike spesifikasjoner, vil anses som fullstendig compatible uansett om du har blitt varslet om slike endringer, selv om det er forskjellig fra den opprinnelige spesifikasjonen eller de som kunden refererer til.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

