

Cat HP J-Hook Mod klips do pręta M4–M12, drut 4,8 - 6,4mm



NUMER KATALOGOWY

CATHPM4Z34

Improved nVent CADDY Cat HP Mod Clip J-Hook with Rod/Wire Clip allows for quick attachment to threaded rod or wire without screws or special tools. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

FUNKCJE

Montaż bez użycia narzędzi

Works with nVent J-Hook Versa-Mount technology from nVent CADDY



ATRYBUTY PRODUKTU

Numer artykułu: 186082


Wykończenie: nVent CADDY Armour

Materiał: Stal sprężysta

Rozmiar pręta (RS): M4;M6;M8;M10;M12

Przekrój drutu: 4.8 - 6.4 mm

Obciążenie statyczne: 130N



OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

Ameryka Północna

+1.800.753.9221

Opcja 1 — obsługa klienta

Opcja 2 — wsparcie

techniczne

Europa

Niderlandy:

+31 800-0200135

Francja:

+33 800 901 793

Europa

Niemcy:

800 1890272

Inne kraje:

+31 13 5835404

APAC

Szanghaj:

+ 86 21 2412 1618/19

Sydney:

+61 2 975 185 00

