

115 Standard Duty Loop Hanger



The 115 Standard Duty Loop Hanger is ideal for suspending stationary, non-insulated pipe lines, including CPVC pipes, in fire sprinkler systems. A knurled insert nut helps simplify vertical adjustments and flared edges on the base (1/2" to 4" sizes) help protect pipes from coming into contact with any sharp edges of the hanger.

CARACTERÍSTICAS

Flared edges help prevent any sharp surfaces from coming into contact with the pipe (1/2" to 4" sizes)

Retained insert nut helps ensure the loop hanger and insert nut stay together

Recommended for the suspension of stationary non-insulated pipe lines

Manufactured to use the minimum rod size permitted by NFPA® for fire sprinkler piping


Conforms with Federal Specification WW-H-171 (Type 10), Manufacturers Standardization Society (MSS) SP-58 (Type 10)

Material: Aço
Acabamento: Pregalvanized



ESPECIFICAÇÕES

Número de catálogo	Número do artigo	NB/DN	Diâmetro externo (OD)	A	B	C	Static Load
1150250EG	182798	65	76 mm	150.8 mm	87.3 mm	50.8 mm	2340N
1150300EG	182804	80	89 mm	166.3 mm	88.2 mm	49.7 mm	2340N
1150400EG	182805	100	114 mm	192.5 mm	100.9 mm	48.9 mm	2890N
1150500EG	182799	125	140 mm	232.7 mm	120 mm	57.1 mm	4450N
1150600EG	182806	150	165 mm	286.6 mm	160.4 mm	84.1 mm	4450N
1150800EG		200	219 mm	327.1 mm	175.1 mm	73.4 mm	4450N



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

