

# Cable Snap Clip

## CARACTERÍSTICAS

Clip snaps on flange and cable snaps into clip



**Material:** Spring Steel  
**Acabamento:** nVent CADDY Armour

## ESPECIFICAÇÕES

Table 1/2


| Número de catálogo | Espessura do flange (FT) | Diâmetro externo (OD) |
|--------------------|--------------------------|-----------------------|
| SC2A               | 1.6 - 4.8 mm             | 6 - 7 mm              |
| SC2B               | 1.6 - 4.8 mm             | 8 - 9 mm              |
| SC2C               | 1.6 - 4.8 mm             | 10 - 11 mm            |
| SC2D               | 1.6 - 4.8 mm             | 12 - 14 mm            |
| SC2E               | 1.6 - 4.8 mm             | 15 - 18 mm            |
| SC2F               | 1.6 - 4.8 mm             | 19 - 24 mm            |
| SC2G               | 1.6 - 4.8 mm             | 25 - 32 mm            |
| SC4A               | 4.8 - 7.1 mm             | 6 - 7 mm              |
| SC4B               | 4.8 - 7.1 mm             | 8 - 9 mm              |
| SC4C               | 4.8 - 7.1 mm             | 10 - 11 mm            |
| SC4D               | 4.8 - 7.1 mm             | 12 - 14 mm            |
| SC4E               | 4.8 - 7.1 mm             | 15 - 18 mm            |
| SC4F               | 4.8 - 7.1 mm             | 19 - 24 mm            |

| Número de catálogo | Espessura do flange (FT) | Diâmetro externo (OD) |
|--------------------|--------------------------|-----------------------|
| SC4G               | 4.8 - 7.1 mm             | 25 - 32 mm            |
| SC8A               | 7.9 - 12.7 mm            | 6 - 7 mm              |
| SC8B               | 7.9 - 12.7 mm            | 8 - 9 mm              |
| SC8C               | 7.9 - 12.7 mm            | 10 - 11 mm            |
| SC8D               | 7.9 - 12.7 mm            | 12 - 14 mm            |
| SC8E               | 7.9 - 12.7 mm            | 15 - 18 mm            |
| SC8F               | 7.9 - 12.7 mm            | 19 - 24 mm            |

Table 2/2

| Número de catálogo | Espessura do flange (FT) | Diâmetro externo (OD) |
|--------------------|--------------------------|-----------------------|
| SC8G               | 7.9 - 12.7 mm            | 25 - 32 mm            |

## DIAGRAMAS



## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

#### América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência  
técnica

#### Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

#### Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

#### APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

