

Branch Line Restraint Structure Attachment to Threaded Hole, 3/8", 1/2" Rod



NÚMERO DE CATÁLOGO

CSBBRS3EG

CARACTERÍSTICAS

Swivel barrel nut accepts 3/8" or 1/2" (M10 or M12) threaded rod

Attaches to concrete anchors or structural attachments with female threads

Can be used for bolting through steel



CARATERÍSTICAS DO PRODUTO

Material: Aço

Acabamento: Electrogalvanized

Tamanho da haste (RS): 0.375;0.5

Altura (H): 28.2 mm

Length (L): 40.4mm


Largura (W): 26.9 mm

Diâmetro do parafuso (Sc): 0.375

Comprimento do parafuso (L): 19mm

DETALHES ADICIONAIS DO PRODUTO

Branch line structural attachments are for restraint only and not for the hanging of fire sprinkler piping.



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

