


Rooftop Pyramid Equipment Support Kit, 4 Post Base, 1257 mm



NÚMERO DE CATÁLOGO

PEK4B

CARACTERÍSTICAS

Kit includes post-base assemblies, frame and equipment-support clamps

Assembles and adjusts to size and height in minutes by one person with one tool

Innovative crossbar and equipment-support clamps enable quick assembly

Integral foam pad provides gentle interface for all roof types

Hot-dip galvanized and UV stabilized for long lasting performance

Assembled support can be lifted as one unit and easily relocated



CARATERÍSTICAS DO PRODUTO

Número do artigo: 360426

Material: Aço; Polypropylene; Polietileno

Acabamento: Hot-Dip Galvanized

Temperatura: -34 to 54.4 °C

Altura (H): 305 - 457 mm

Length (L): 1257mm

Post Base (A): 314 mm x 4 pc

Square Tube (B): 1067 mm x 2 pc

Cross Bar Assembly (C): 1232 mm x 2 pc

Largura (W): 1588 mm

Surface Area: 0.36m²

Peso unitário: 36 kg



Ultimate Static Load (F): 4980N

Static Load Safety Factor: 3:1

DETALHES ADICIONAIS DO PRODUTO

Static load must be stable and uniformly distributed across frame.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com

