

Rooftop Pyramid ST Bridge Assembly, 610 mm

NÚMERO DE CATÁLOGO

PSB24A

CARACTERÍSTICAS

Ideal for supporting multiple pipe runs, cable tray and air handling units

Foam bottom offers low abrasion interface for better roof membrane protection


Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Ready to use out of the box, saving installation time and labor

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Hot-dip galvanized and UV stabilized for long lasting performance



CARATERÍSTICAS DO PRODUTO

Número do artigo: 360475

Material: Polietileno;Polypropylene;Aço

Acabamento: Hot-Dip Galvanized

Temperatura: -45 to 65 °C

Static Load Safety Factor: 3:1

Comprimento 1 (L1): 610 mm

Comprimento 2 (L2): 673 mm

Altura (H): 142 mm

Largura (W): 203 mm

Surface Area: 118709mm²


Peso unitário: 2 kg

Static Load: 8900N

DETALHES ADICIONAIS DO PRODUTO

Static loads are assumed to be uniformly distributed.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/CADDY

