

nVent CADDY Speed Link SLS with Wedge Anchor, 2 mm Wire, 3 m Length



NÚMERO DE CATÁLOGO

SLS2L3WA6

CARACTERÍSTICAS

Complete system includes wire, locking device and wedge anchor from Powers Fasteners, Inc.

Quickly and easily attaches into cracked and non-cracked concrete

Installs in strut profiles without the need to insert fingers or tools into the strut

Finger tightening of nut secures the locking device into position without tools

No special tools required

ETA-13/0355 assessment available for wedge anchor from Powers Fasteners, Inc



CARATERÍSTICAS DO PRODUTO

Número do artigo: 196759

Material: Aço; Polypropylene; Liga de zinco

Acabamento: Electro galvanized

Static Load Safety Factor: 5:1

Em conformidade com: SMACNA HVAC-DCS

Wire Rope Diameter: 2 mm

Wire Rope Length: 3m

Length (L): 63.5mm

Diâmetro da broca: 6mm

Profundidade do orifício de perfuração: 60mm

Embedment Depth: 55 mm Min

Static Load: 270N

Tamanho da rosca (TS): M8

Altura 1 (H1): 53mm

Altura 2 (H2): 43.5mm

Largura (W): 16 mm

Espessura (T): 4 mm Max

Tamanho do orifício (HS): 8 - 10 mm


Slot Size (SS): 8 x 6.5 mm - 8 x 10 mm

DETALHES ADICIONAIS DO PRODUTO

The 2 mm locking device is compatible with C-Channel Types E0 and E0L.

Total load per wire on a multi-tier trapeze must not exceed static load.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência
técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

