

Hammer-On Flange Clip, Bottom Mount with Stud



CARACTERÍSTICAS

Can be used to support boxes, fixtures or other applications from beam flanges

Captive threaded stud minimizes the need for additional hardware

Assorted attachment points provided to reduce inventory


Requires only a hammer to install

Material: Spring Steel
Acabamento: nVent CADDY Armour



ESPECIFICAÇÕES

Número de catálogo	Espessura do flange (FT)	Tamanho da haste (RS)	Diâmetro do parafuso (Sc)	Comprimento do parafuso (L)	Static Load 1 (F1)	Static Load 2 (F2)	Static Load 3 (F3)
M24S	3 - 8 mm	0.25	0.25	9.5mm	440N	330N	110N
M58S	8 - 14 mm	0.25	0.25	9.5mm	440N	330N	110N
M912S	14 - 20 mm	0.25	0.25	9.5mm	440N	330N	110N



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

