

Improved nVent CADDY Cat HP J-Hook with C Purlin Clip



The Improved nVent CADDY Cat HP J-Hook with C Purlin Clip is an innovative assembly featuring a combination of the Improved nVent CADDY Cat HP J-Hook with a C Purlin Clip attachment. The Assembly enhances cable management by offering superior stability and customization options, while minimizing inventory impact and maximizing flexibility across diverse installation environments.

Engineered for high-performance data cable management, this system supports Cat 5e, Cat 6, Cat 6A, Cat 7, and fiber optic cables with superior fill capacity and load ratings compared to most non-continuous alternatives. The Assemblies' rounded edges ensure proper bend radius support, protecting cable integrity and optimizing performance.

CARACTERÍSTICAS

Hammer-on or install from the floor with the VAFT tool

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Número do artigo	Material	Acabamento	Diâmetro	Area	Cable Capacity, Cat 5e
CAT16HPVF14	181145	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	25 mm	690mm ²	20

Número de catálogo	Número do artigo	Material	Acabamento	Diâmetro	Area	Cable Capacity, Cat 5e
CAT21HPVF14	181249	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	33.3 mm	1174mm ²	50
CAT32HPVF14	181146	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	50 mm	2561mm ²	90
CAT48HPVF14	181147	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	75 mm	5974mm ²	200
CAT64HPVF14	181148	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	100 mm	9987mm ²	330

Table 2/2

Número de catálogo	Número do artigo	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	Espessura do flange	Static Load
CAT16HPVF14	181145	15	10	1.5 - 6 mm	270N
CAT21HPVF14	181249	40	25	1.5 - 6 mm	270N
CAT32HPVF14	181146	60	35	1.5 - 6 mm	270N
CAT48HPVF14	181147	150	80	1.5 - 6 mm	270N
CAT64HPVF14	181148	220	140	1.5 - 6 mm	270N

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221
Opção 1 – Apoio ao cliente
Opção 2 – Assistência técnica

Europa

Países Baixos:
+31 800-0200135
França:
+33 800 901 793

Europa

Alemanha:
800 1890272
Outros países:
+31 13 5835404

APAC

Xangai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

