

nVent CADDY Speed Link Y-Toggle with Eyelet Extension



CARACTERÍSTICAS

Attaches to clearance holes in a variety of structures or hanging devices

Ideal for supporting lighting fixtures

Y-design provides improved stability

Material: Aço
Acabamento: Electrogalvanized
Static Load Safety Factor: 5:1
Wire Rope Diameter: 1.5 mm





ESPECIFICAÇÕES

Número de catálogo	Número do artigo	Wire Rope "Y" Length (YL)	A	B	Static Load	Certifications
SLD15Y200	195999	0.2m	39 mm	5 mm	195N	UL, cUL
SLD15Y300	196000	0.3m	39 mm	5 mm	195N	UL, cUL
SLD15Y500	195960	0.5m	39 mm	5 mm	195N	UL, cUL, ITB

DETALHES ADICIONAIS DO PRODUTO

nVent CADDY Speed Link locking device not included.



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

