

SN Series Nut



CARACTERÍSTICAS

Allows side mounting of nut to threaded rod

Reduces the need for threading compared to standard nuts and washers

Ideal for retrofit projects, such as trapeze installations, where disassembly of the support system is not desired



Works with slightly damaged threads and minor burrs on the threaded rod

Reduces installation time up to 50%

Material: Aço
Acabamento: Electrogalvanized

ESPECIFICAÇÕES

Número de catálogo	Tamanho da haste (RS)	Altura (H)	Largura hexagonal (W)	Static Load
SN25	0.25	14mm	16 mm	2200N
SN37	0.375	19mm	19 mm	6000N
SN50	0.5	23mm	25 mm	10000N



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

