


34566-720

CARACTERÍSTICAS

Aluminum extrusion, anodized finish, conductive contact surface



Combinations of horizontal rails and side panels

$u^{*}=0$ can be combined, $u^{*}=1$ combination not recommended

Rail type		-	+	+	side rail 1 (right)
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Horizontal rail		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+
		+	+	+	+
Side panel		+	+	+	+



CARATERÍSTICAS DO PRODUTO

Net Weight: 0.056kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALHES ADICIONAIS DO PRODUTO

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

