

# EuropacPRO 19" Subrack Kit for Railway, Shielded, EN 50155

Subrack for Railway applications, conform to EN50155 standard, shielded versions.



## CARACTERÍSTICAS

Shock and vibration tested to EN 50155, part 12.2.11

The 19" bracket is firmly fixed to the side panel (tox-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

The double 19" screwing position adds to additionally safety (NFF standard)

IP 20, in accordance with IEC 60529

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Aluminum construction

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>Em conformidade com:</b> | IEC 60297-3-103; EN 50155 part 12.2.11 |
| <b>Profundidade:</b>        | 235mm                                  |
| <b>EMC Shielding:</b>       | Sim                                    |
| <b>Material:</b>            | Aluminio                               |
| <b>Product Type:</b>        | Subrack/Chassis                        |
| <b>Rack Width:</b>          | 84HP                                   |
| <b>Static Load:</b>         | 15kg                                   |



## ESPECIFICAÇÕES

Table 1/2

| Número de catálogo | Rack Height | Quantidade por embalagem | For Mounting | Board Depth | Gasket Type | Shock and Vibration Tolerance |
|--------------------|-------------|--------------------------|--------------|-------------|-------------|-------------------------------|
| 21500-079          | 3U          | 1                        | Backplane    | 220mm       | Textile EMC | 5g (force)                    |
| 21500-080          | 6U          | 1                        | Backplane    | 220mm       | Textile EMC | 5g (force)                    |

Table 2/2

| Número de catálogo | Inclui alça | Instalação | Acabamento           |
|--------------------|-------------|------------|----------------------|
| 21500-079          | Sim         | Rack       | Anodized, Passivated |
| 21500-080          | Sim         | Rack       | Anodized, Passivated |

## DETALHES ADICIONAIS DO PRODUTO

Test reports are available online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.