

# Plug-In Unit Kit With IEL Handle, Shielded, Black, 6 U



Plug-in unit, with IEL inserter/extractor black handle, 6 U, front assembly. The U-shaped front panel enable shielding with a textile gasket.

## CARACTERÍSTICAS

U-shaped front panel for textile gasket

Suitable for insertion and extraction forces up to 700 N (per pair)

Enable the installation of a microswitch

Enable the installation of coding pegs in accordance with IEC 60297-3-103/ IEEE 1101.10

**Acabamento:** Anodized; Passivated  
**Material:** Alumínio  
**Product Type:** Front Panel  
**Tipo:** Front Panel with Handle (PIU)



## ESPECIFICAÇÕES

Table 1/2


| Número de catálogo | Rack Width | Quantidade por embalagem | Tipo de alça | Instalação                       | Gasket Type | Front Finish |
|--------------------|------------|--------------------------|--------------|----------------------------------|-------------|--------------|
| 20848-592          | 4HP        | 1                        | IEL          | Screw-on Front, Screw-on Rear IO | Textile EMC | Anodized     |
| 20848-594          | 6HP        | 1                        | IEL          | Screw-on Front, Screw-on Rear IO | Textile EMC | Anodized     |
| 20848-596          | 8HP        | 1                        | IEL          | Screw-on Front, Screw-on Rear IO | Textile EMC | Anodized     |
| 20848-597          | 10HP       | 1                        | IEL          | Screw-on Front, Screw-on Rear IO | Textile EMC | Anodized     |
| 20848-598          | 12HP       | 1                        | IEL          | Screw-on Front, Screw-on Rear IO | Textile EMC | Anodized     |

Table 2/2

| Número de catálogo | Rear Finish | Treated Edges | Em conformidade com                                            | EMC Shielding | Altura (H) | Rack Height | Largura (W) |
|--------------------|-------------|---------------|----------------------------------------------------------------|---------------|------------|-------------|-------------|
| 20848-592          | Etched      | Não           | IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | Sim           | 261.8mm    | 6U          | 20mm        |
| 20848-594          | Etched      | Não           | IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | Sim           | 261.8mm    | 6U          | 30.1mm      |
| 20848-596          | Etched      | Não           | IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | Sim           | 261.8mm    | 6U          | 40.3mm      |
| 20848-597          | Etched      | Não           | IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | Sim           | 261.8mm    | 6U          | 50.5mm      |
| 20848-598          | Etched      | Não           | IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | Sim           | 261.8mm    | 6U          | 60.6mm      |

## DIAGRAMAS

6 U



## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

