


Rear Panel for RatiopacPRO/PropacPRO, Perforated, Retrofit Shielding



The perforated rear panel, Al, 2.5 mm is unshielded. The rear side is conductive.

CARACTERÍSTICAS

Rear panel, Al, 2.5 mm, front: anodized, rear: conductive; unshielded

Enables mounting on horizontal rails

Acabamento:	Anodized; Passivated
Material:	Aluminio
Família de produtos:	RatiopacPRO; RatiopacPRO AIR
Product Type:	Side Panel
Tipo:	Rear Panel
Works With:	Cases



ESPECIFICAÇÕES

Número de catálogo	Rack Height	Rack Width	Quantidade por embalagem	Altura	Largura
20848-680	2U	42HP	1	83.5mm	213mm
20848-681	2U	63HP	1	83.5mm	319.7mm
20848-633	3U	28HP	1	123.4mm	141.9mm
20848-634	3U	42HP	1	123.4mm	213mm
20848-635	3U	63HP	1	123.4mm	319.7mm
20848-636	3U	84HP	1	123.4mm	426.4mm
20848-657	4U	42HP	1	168.9mm	213mm
20848-658	4U	63HP	1	168.9mm	319.7mm
20848-659	4U	84HP	1	168.9mm	426.4mm
20848-643	6U	84HP	1	256mm	426.4mm
20848-640	6U	28HP	1	256mm	141.9mm

Número de catálogo	Rack Height	Rack Width	Quantidade por embalagem	Altura	Largura
20848-641	6U	42HP	1	256mm	213mm
20848-642	6U	63HP	1	256mm	319.7mm
20848-656	4U	28HP	1	168.9mm	141.9mm
20848-679	2U	28HP	1	83.5mm	141.9mm
20848-682	2U	84HP	1	83.5mm	426.4mm
20848-744	5U	28HP	1	220mm	141.9mm
20848-745	5U	42HP	1	220mm	213mm
20848-746	5U	63HP	1	220mm	319.7mm
20848-747	5U	84HP	1	220mm	426.4mm

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.