

# 115M Standard Duty Loop Hanger



The 115M Standard Duty Loop Hanger is ideal for suspending stationary, non-insulated pipe lines, including CPVC pipes, in fire sprinkler systems. A knurled insert nut helps simplify vertical adjustments and flared edges on the base (1/2" to 4" sizes) help protect pipes from coming into contact with any sharp edges of the hanger.

## CARACTERÍSTICAS

Flared edges help prevent any sharp surfaces from coming into contact with the pipe (1/2" to 4" sizes)

Retained insert nut helps ensure the loop hanger and insert nut stay together

Recommended for the suspension of stationary non-insulated pipe lines

Manufactured to use the minimum rod size permitted by NFPA® for fire sprinkler piping

Conforms with Federal Specification WW-H-171 (Type 10), Manufacturers Standardization Society (MSS) SP-58 (Type 10)

**Material:** Aço  
**Acabamento:** Pregalvanized




## ESPECIFICAÇÕES

Table 1/2

| Número de catálogo | Número do artigo | NB/DN | Diâmetro externo (OD) | Tamanho da haste (RS) | A        | B        |
|--------------------|------------------|-------|-----------------------|-----------------------|----------|----------|
| 115M0050EG         | 597860           | 15    | 21.3 mm               | M10                   | 71 mm    | 28.6 mm  |
| 115M0075EG         | 597870           | 20    | 26.9 mm               | M10                   | 75.9 mm  | 30.2 mm  |
| 115M0100EG         | 597880           | 25    | 33.7 mm               | M10                   | 82.5 mm  | 34.9 mm  |
| 115M0125EG         | 597890           | 32    | 42.4 mm               | M10                   | 90.6 mm  | 38.1 mm  |
| 115M0150EG         | 597900           | 40    | 48.3 mm               | M10                   | 96.7 mm  | 41.3 mm  |
| 115M0200EG         | 597910           | 50    | 60.3 mm               | M10                   | 108.6 mm | 47.6 mm  |
| 115M0250EG         | 597920           | 65    | 76 mm                 | M10                   | 150.8 mm | 87.3 mm  |
| 115M0300EG         | 597930           | 80    | 89 mm                 | M10                   | 166.3 mm | 88.2 mm  |
| 115M0400EG         | 597940           | 100   | 114 mm                | M10                   | 192.5 mm | 100.9 mm |

| Número de catálogo | Número do artigo | NB/DN | Diâmetro externo (OD) | Tamanho da haste (RS) | A        | B        |
|--------------------|------------------|-------|-----------------------|-----------------------|----------|----------|
| 115M0500EG         | 597950           | 125   | 140 mm                | M12                   | 232.7 mm | 120 mm   |
| 115M0600EG         | 597960           | 150   | 165 mm                | M12                   | 286.6 mm | 160.4 mm |
| 115M0800EG         | 597970           | 200   | 219 mm                | M12                   | 327.1 mm | 175.1 mm |

| Table 2/2          |                  |         |                          |                                                   |
|--------------------|------------------|---------|--------------------------|---------------------------------------------------|
| Número de catálogo | Número do artigo | C       | Ultimate Static Load (F) | Certifications                                    |
| 115M0050EG         | 597860           | 25.4 mm | 5000N                    | cUL, UL, ITB                                      |
| 115M0075EG         | 597870           | 23.9 mm | 5000N                    | cUL, UL, FM Approved, Pipe Hanger Components, ITB |
| 115M0100EG         | 597880           | 24.1 mm | 5000N                    | cUL, UL, FM Approved, Pipe Hanger Components, ITB |
| 115M0125EG         | 597890           | 24.1 mm | 5000N                    | ITB, cUL, FM Approved, Pipe Hanger Components, UL |
| 115M0150EG         | 597900           | 24.1 mm | 5000N                    | ITB, cUL, FM Approved, Pipe Hanger Components, UL |
| 115M0200EG         | 597910           | 23.9 mm | 5000N                    | cUL, UL, ITB, FM Approved, Pipe Hanger Components |
| 115M0250EG         | 597920           | 50.8 mm | 14000N                   | FM Approved, Pipe Hanger Components, cUL, ITB, UL |
| 115M0300EG         | 597930           | 49.7 mm | 14000N                   | FM Approved, Pipe Hanger Components, cUL, ITB, UL |
| 115M0400EG         | 597940           | 48.9 mm | 14000N                   | ITB, cUL, UL, FM Approved, Pipe Hanger Components |
| 115M0500EG         | 597950           | 57.1 mm | 20000N                   | ITB, UL, cUL, FM Approved, Pipe Hanger Components |
| 115M0600EG         | 597960           | 84.1 mm | 20000N                   | UL, FM Approved, Pipe Hanger Components, ITB, cUL |
| 115M0800EG         | 597970           | 73.4 mm | 20000N                   | cUL, UL, FM Approved, Pipe Hanger Components, ITB |



### AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

#### América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

#### Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

#### Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

#### APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

