

Drop-In Anchor



CARACTERÍSTICAS

Internal thread provides easy removal and serviceability

Installs flush or below the base surface

Suitable for redundant non-structural systems on cracked and non-cracked concrete

Fire resistance class R30-R120 for design of anchorages under exposure to fire



ESPECIFICAÇÕES


Número de catálogo	Número do artigo	Material	Acabamento	Tamanho do orifício (HS)	Length (L)	Diâmetro da broca	Certifications
CAM10040	593200	Aço	Electrogalvanized	10 mm	40mm	12mm	VdS, CE, 14-0135, FM Approved, Anchor, CE, 14-0068
CAM10040S6	401155	Stainless Steel 316 (EN 1.4401)		10 mm	40mm	12mm	CE, 14-0068, VdS
CAM12050	400415	Aço	Electrogalvanized	12 mm	50mm	15mm	CE, 14-0068, FM Approved, Anchor, CE, 14-0135, VdS
CAM6030	593180	Aço	Electrogalvanized	6 mm	30mm	8mm	CE, 14-0068, CE, 14-0135
CAM8030	593190	Aço	Electrogalvanized	8 mm	30mm	10mm	VdS, CE, 14-0068, CE, 14-0135

Número de catálogo	Número do artigo	Material	Acabamento	Tamanho do orifício (HS)	Length (L)	Diâmetro da broca	Certifications
CAM8030S6	401154	Stainless Steel 316 (EN 1.4401)		8 mm	30mm	10mm	CE, 14-0068, VdS

Characteristic Axial Loads from ETA 14-0135			
Part Number	Cracked Concrete C20/25	Non-Cracked Concrete C20/25	Standard Embedment Depth
CAM6030	-	2.50 kN	25 mm
CAM8030	-	3.30 kN	30 mm
CAM10040	-	4.40 kN	40 mm
CAM12050	-	6.10 kN	50 mm
CAM8030S6	-	-	-
CAM10040S6	-	-	-

Characteristic Axial Loads from ETA 14-0068 - for redundant non-structural systems			
Part Number	Cracked Concrete C20/25	Non-Cracked Concrete C20/25	Standard Embedment Depth
CAM6030	0.80 kN	0.80 kN	25 mm
CAM8030	1.20 kN	1.20 kN	30 mm
CAM10040	1.70 kN	1.70 kN	40 mm
CAM12050	2.60 kN	2.60 kN	50 mm
CAM8030S6	1.20 kN	1.20 kN	25 mm
CAM10040S6	1.70 kN	1.70 kN	40 mm

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

