

# nVent CADDY Superklip, 24.8–27.8 mm OD, 3/4" Pipe



## NÚMERO DE CATÁLOGO

**389006**

## CARACTERÍSTICAS

Closes and locks automatically when the pipe, tube or cable is inserted

One-piece clamp for fast and convenient installation

Fasten with either wood screw, dual threaded screw with or without collar, nail with collar, threaded rod, mounting plate or shot-fire bracket

## CARATERÍSTICAS DO PRODUTO

Número do artigo: 389006

Material: Xenoy®

Temperatura: -25 to 90 °C



Diâmetro externo (OD): 24.8 - 27.8 mm

Tamanho do tubo: 3/4"

B: 20.2 mm

C: 45.1 mm

Static Load: 240N



## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

### Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

### Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

### APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

