


4G24 Twist Clip with Stud, CADDY ARMOUR, Gray, 16 mm Screw, 1.5 mm Flange, 24 mm T-Grid



NÚMERO DE CATÁLOGO

4G24M16

CARACTERÍSTICAS

- Supports electrical fixtures from acoustical T-grid
- No tools required for installation
- Fast, easy and secure twist-on installation
- Designed to reduce scratching of T-grid
- Nut sold separately



CARATERÍSTICAS DO PRODUTO

Número do artigo: 171710

Material: Spring Aço;Aço

Acabamento: nVent CADDY Armour

Cor: Gray


Comprimento do parafuso (L): 16mm

Espessura do flange (FT): 1.5 mm

T-Grid Size: 24mm

Diâmetro do parafuso (Sc): 6

Static Load: 220N



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

