

# 4G24 Twist Clip with Stud, Painted, White, 16 mm Screw, 1.5 mm Flange, 24 mm T-Grid

## NÚMERO DE CATÁLOGO

**4G24M16WHSP25**



## CARACTERÍSTICAS

Supports electrical fixtures from acoustical T-grid

No tools required for installation

Fast, easy and secure twist-on installation

Designed to reduce scratching of T-grid

Nut sold separately



## CARATERÍSTICAS DO PRODUTO

Número do artigo: 172290

Material: Spring Aço;Aço

Acabamento: Painted

Cor: Branco


Comprimento do parafuso (L): 16mm

Espessura do flange (FT): 1.5 mm

T-Grid Size: 24mm

Diâmetro do parafuso (Sc): 6

Static Load: 220N



### AVISO

---

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

#### **América do Norte**

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência  
técnica

#### **Europa**

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

#### **Europa**

Alemanha:

800 1890272

Outros países:

+31 13 5835404

#### **APAC**

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

