

Cat HP J-Hook Mod clip para barra M4–M12, fio 4,8 - 6,4mm



NÚMERO DE CATÁLOGO

CATHPM4Z34

Improved nVent CADDY Cat HP Mod Clip J-Hook with Rod/Wire Clip allows for quick attachment to threaded rod or wire without screws or special tools. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

CARACTERÍSTICAS

Tool-free assembly

Works with nVent J-Hook Versa-Mount technology from nVent CADDY



CARATERÍSTICAS DO PRODUTO

Número do artigo: 186082


Acabamento: nVent CADDY Armour

Material: Spring Steel

Tamanho da haste (RS): M4;M6;M8;M10;M12

Tamanho do fio: 4.8 - 6.4 mm

Static Load: 130N



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

