

Metal Pressure Clip, 10 Cable, 4.8 mm Hole

NÚMERO DE CATÁLOGO

PKM10H3

CARACTERÍSTICAS

Ideal for smaller runs of cables

Flexible clip retains shape and allows for cables to be inserted after installation

Rounded edges help prevent cable damage

Cables are neatly installed providing a consistent and professional appearance

Low profile allows for installations in tight spaces



CARATERÍSTICAS DO PRODUTO

Número do artigo: 182044

Material: Spring Steel

Acabamento: nVent CADDY Armour



Cable Capacity: 10

Tamanho do orifício (HS): 4.8 mm

Length (L): 171.5mm

DETALHES ADICIONAIS DO PRODUTO

Supports cable diameters up to 1/2" (13 mm) when installed with a standard 1/4" (6 mm) washer.



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

