

H-Ti/T Rod to Flange Clip



CARACTERÍSTICAS

Suspends threaded rod from beam flanges

Threaded rod hanger can swivel to provide a vertical dropdown

Requires only a hammer to install

Material: Spring Steel
Acabamento: nVent CADDY Armour




ESPECIFICAÇÕES

Número de catálogo	Número do artigo	Tamanho do orifício (HS)	Hole Type	Espessura do flange (FT)	Static Load	Certifications
160000	160000	11 mm	Plain	2 - 3 mm	700N	ITB
160010	160010	11 mm	Plain	3 - 8 mm	900N	ITB
160030	160030	11 mm	Plain	14 - 20 mm	900N	ITB
M10TI24	175000	10 mm	Threaded	3 - 8 mm	900N	ITB
M10TI58	175010	10 mm	Threaded	8 - 14 mm	900N	ITB
M10TI912	175020	10 mm	Threaded	14 - 20 mm	900N	ITB
M6TI24	174820	6 mm	Threaded	3 - 8 mm	900N	ITB, CE, 4QTI24, 4QTI58, M6TI24, M6TI58
M6TI24R5	191024	6 mm	Threaded	3 - 8 mm	900N	

Número de catálogo	Número do artigo	Tamanho do orifício (HS)	Hole Type	Espessura do flange (FT)	Static Load	Certifications
M6TI4	174810	6 mm	Threaded	2 - 3 mm	700N	ITB
M6TI58	174830	6 mm	Threaded	8 - 14 mm	900N	ITB, CE, 4QTI24, 4QTI58, M6TI24, M6TI58
M6TI912	174840	6 mm	Threaded	14 - 20 mm	900N	ITB
M8TI24	174910	8 mm	Threaded	3 - 8 mm	900N	ITB
M8TI4	174900	8 mm	Threaded	2 - 3 mm	700N	ITB
M8TI58	174920	8 mm	Threaded	8 - 14 mm	900N	ITB
M8TI912	174930	8 mm	Threaded	14 - 20 mm	900N	ITB
T1058	160020	11 mm	Plain	8 - 14 mm	900N	ITB

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

