


nVent CADDY Macrofix Insulated M8



CARACTERÍSTICAS

Return-lip on the hanger prevents the rubber from detaching, eliminating rework during installation

Plastic washer prevents screws from falling out during installation

Combo head bolt works with slotted, hex, or Phillips drivers

Longer ears position the screw farther from the hanger, improving tool clearance when the screw is tightened

Screw length has been optimized to accommodate an increased pipe range, reducing inventory

Halogen-free

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

Material: EPDM-SBR Rubber;Aço
Acabamento: Electrogalvanized
Temperatura: -50 to 110 °C



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Número do artigo	Diâmetro externo (OD)	NB/D N	Tamanho da haste (RS)	Largura (W)	Espessura (T)
MFE015	586201	11 - 15 mm	8	M8	20 mm	1 mm
MFE019	586202	15 - 19 mm	10	M8	20 mm	1 mm
MFE025	586203	19 - 25 mm	15	M8	20 mm	1 mm
MFE031	586204	25 - 31 mm	20	M8	20 mm	1 mm
MFE037	586205	31 - 37 mm	25	M8	20 mm	1 mm
MFE044	586206	37 - 44 mm	32	M8	20 mm	1 mm
MFE050	586207	44 - 50 mm	40	M8	20 mm	1.25 mm

Número de catálogo	Número do artigo	Diâmetro externo (OD)	NB/D N	Tamanho da haste (RS)	Largura(W)	Espessura (T)
MFE058	586208	50 - 58 mm		M8	20 mm	1.25 mm
MFE068	586209	58 - 68 mm	50	M8	20 mm	1.25 mm


Table 2/2

Número de catálogo	Número do artigo	Diâmetro do parafuso (Sc)	Comprimento do parafuso (L)	Static Load
MFE015	586201	6	17mm	1000N
MFE019	586202	6	17mm	1000N
MFE025	586203	6	22mm	1000N
MFE031	586204	6	22mm	1000N
MFE037	586205	6	22mm	1000N
MFE044	586206	6	27mm	1000N
MFE050	586207	6	27mm	1500N
MFE058	586208	6	27mm	1500N
MFE068	586209	6	32mm	1500N

DETALHES ADICIONAIS DO PRODUTO

Lining is EPDM rubber.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência
técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

