

# nVent CADDY Speed Link SLK with Wedge Anchor



## CARACTERÍSTICAS

Complete system includes wire, locking device and wedge anchor from fischerwerke GmbH &Co. KG

Quickly and easily attaches into cracked and non-cracked concrete

No special tools required

ETA 06/0175 approval available from fischerwerke GmbH &Co. KG

|                                                |                                 |
|------------------------------------------------|---------------------------------|
| <b>Material:</b>                               | Aço;Polypropylene;Liga de zinco |
| <b>Acabamento:</b>                             | Electrogalvanized               |
| <b>Static Load Safety Factor:</b>              | 5:1                             |
| <b>Diâmetro da broca:</b>                      | 6mm                             |
| <b>Profundidade do orifício de perfuração:</b> | 31mm                            |
| <b>Embedment Depth:</b>                        | 25 mm Min                       |

## ESPECIFICAÇÕES

Table 1/2


| Número de catálogo | Número do artigo | Wire Rope Diameter | Wire Rope Length | Length (L) | Altura (H) | Largura (W) |
|--------------------|------------------|--------------------|------------------|------------|------------|-------------|
| SLK15L2WA6         | 196671           | 1.5 mm             | 2m               | 54mm       | 55 mm      | 19 mm       |
| SLK15L3WA6         | 196672           | 1.5 mm             | 3m               | 54mm       | 55 mm      | 19 mm       |
| SLK2L2WA6          | 196734           | 2 mm               | 2m               | 54mm       | 55 mm      | 19 mm       |
| SLK2L3WA6          | 196735           | 2 mm               | 3m               | 54mm       | 55 mm      | 19 mm       |

Table 2/2

| Número de catálogo | Número do artigo | Espessura (T) | Ângulo (a) | Static Load |
|--------------------|------------------|---------------|------------|-------------|
| SLK15L2WA6         | 196671           | 12.5 mm       | 90 ° Max   | 195N        |
| SLK15L3WA6         | 196672           | 12.5 mm       | 90 ° Max   | 195N        |

| Número de catálogo | Número do artigo | Espessura (T) | Ângulo (a) | Static Load |
|--------------------|------------------|---------------|------------|-------------|
| SLK2L2WA6          | 196734           | 12.5 mm       | 90 ° Max   | 300N        |
| SLK2L3WA6          | 196735           | 12.5 mm       | 90 ° Max   | 300N        |

## DIAGRAMAS



## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### América do Norte

+1 800 753 9221  
Opção 1 – Apoio ao cliente  
Opção 2 – Assistência  
técnica

### Europa

Países Baixos:  
+31 800-0200135  
França:  
+33 800 901 793

### Europa

Alemanha:  
800 1890272  
Outros países:  
+31 13 5835404

### APAC

Xangai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/GRDDT](http://nVent.com/GRDDT)

