

nVent CADDY Superfix 243 M8



CARACTERÍSTICAS

Includes easy closing mechanism

Combo head bolt works with slotted, hex, or Phillips drivers

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

Material: Aço;EPDM-SBR Rubber
Acabamento: Electro galvanized
Cor: Black
Temperatura: -50 to 110 °C



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Número do artigo	Diâmetro externo (OD)	NB/D N	Tamanho da haste (RS)	Largura (W)	Espessura (T)
SXE019	400056	15 - 19 mm	10	M8	20 mm	1.5 mm
SXE023	400057	21 - 23 mm	15	M8	20 mm	1.5 mm
SXE028	400058	26 - 28 mm	20	M8	20 mm	1.5 mm
SXE035	400059	32 - 35 mm	25	M8	20 mm	1.5 mm
SXE043	400060	40 - 43 mm	32	M8	20 mm	1.5 mm
SXE052	400062	48 - 52 mm	40	M8	20 mm	1.5 mm
SXE058	589310	54 - 58 mm		M8	20 mm	2 mm
SXE061	589320	57 - 61 mm	50	M8	20 mm	2 mm
SXE014	400055	12 - 14 mm	8	M8	20 mm	1.5 mm


Table 2/2

Número de catálogo	Número do artigo	Diâmetro do parafuso (Sc)	Comprimento do parafuso (L)	Static Load
SXE019	400056	6	27mm	1000N
SXE023	400057	6	27mm	1000N
SXE028	400058	6	27mm	1000N
SXE035	400059	6	27mm	1000N
SXE043	400060	6	32mm	1000N
SXE052	400062	6	32mm	1300N
SXE058	589310	6	32mm	1300N
SXE061	589320	6	32mm	1300N
SXE014	400055	6	27mm	1000N

DETALHES ADICIONAIS DO PRODUTO

Lining is EPDM rubber.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência
técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

