


Speedway Cable Ladder Flat Elbow, 45°



CARACTERÍSTICAS

Creates a 45° corner change in cable tray direction

Provides optimal support for high-performance low voltage and data cables

Innovative SPEEDLOK integrated coupling system

Safety edge protects cables during installation

Slotted side channel, eliminating field drilling for cut-to-length applications

IEC 61537 load rating and earthing compliant


Responsive design and layout services, including seismic

Material: Aço
Acabamento: Hot-Dip Galvanized



ESPECIFICAÇÕES

Número de catálogo	Número do artigo	Largura (W)	Ângulo (a)	A	B	C	D
CL110X150FE45HD	840100	150 mm	45 °	326 mm	460 mm	80 mm	110 mm
CL110X300FE45HD	840110	300 mm	45 °	476 mm	566 mm	80 mm	110 mm
CL110X450FE45HD	840120	450 mm	45 °	626 mm	673 mm	80 mm	110 mm
CL110X600FE45HD	840130	600 mm	45 °	776 mm	779 mm	80 mm	110 mm
CL110X750FE45HD	840140	750 mm	45 °	926 mm	885 mm	80 mm	110 mm
CL110X900FE45HD	840150	900 mm	45 °	1076 mm	991 mm	80 mm	110 mm



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

