


Speedway Cable Ladder Flat Elbow, 90°



CARACTERÍSTICAS

Creates a 90° corner change in cable tray direction

Provides optimal support for high-performance low voltage and data cables

Innovative SPEEDLOK integrated coupling system

Safety edge protects cables during installation

Slotted side channel, eliminating field drilling for cut-to-length applications

IEC 61537 load rating and earthing compliant


Responsive design and layout services, including seismic

Material: Aço
Acabamento: Hot-Dip Galvanized



ESPECIFICAÇÕES

Número de catálogo	Número do artigo	Largura (W)	Ângulo (a)	A	B	C
CL110X150FE90HD	840200	150 mm	90 °	545 mm	545 mm	80 mm
CL110X300FE90HD	840210	300 mm	90 °	695 mm	695 mm	80 mm
CL110X450FE90HD	840220	450 mm	90 °	845 mm	845 mm	80 mm
CL110X600FE90HD	840230	600 mm	90 °	995 mm	995 mm	80 mm
CL110X750FE90HD	840240	750 mm	90 °	1145 mm	1145 mm	80 mm
CL110X900FE90HD	840250	900 mm	90 °	1295 mm	1295 mm	80 mm



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

