

Speedway Cable Ladder Outside Riser, 90°



CARACTERÍSTICAS

Creates a 90° outside riser elevation change for cable tray

Provides optimal support for high-performance low voltage and data cables

Innovative SPEEDLOK integrated coupling system

Safety edge protects cables during installation

Slotted side channel, eliminating field drilling for cut-to-length applications

IEC 61537 load rating and earthing compliant



Responsive design and layout services, including seismic

Material: Aço
Acabamento: Hot-Dip Galvanized



ESPECIFICAÇÕES

Número de catálogo	Número do artigo	Largura (W)	Ângulo (a)	A	B	C	D
CL110X150R90HD	840600	150 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X300R90HD	840610	300 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X450R90HD	840620	450 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X600R90HD	840630	600 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X750R90HD	840640	750 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X900R90HD	840650	900 mm	90 °	410 mm	410 mm	580 mm	80 mm



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

