


Uniklip Equal Tee



CARACTERÍSTICAS

Creates a quick and easy equal tee pathway intersection

Provides optimal support for high-performance low voltage and data cables

Innovative UNIKLIP installation system that installs up to three times faster

IEC 61537 load rating and earthing compliant

No field cutting or modifications required; just drop it in and keep installing the cable tray

Eliminates safety related concerns around field cutting

Tool-free, integrated couplers with Uniklip

Material: Aço
Acabamento: Pregalvanized



ESPECIFICAÇÕES

Número de catálogo	Número do artigo	Largura (W)	Profundidade (D)	Length (L)	A	B
PCT50X050ET	850300	50 mm	49mm	375mm	202 mm	91 mm
PCT50X075ET	850310	75 mm	49mm	405mm	228 mm	91 mm
PCT50X100ET	850320	100 mm	49mm	425mm	253 mm	91 mm
PCT50X150ET	850330	150 mm	49mm	475mm	303 mm	91 mm
PCT50X225ET	850340	225 mm	49mm	550mm	378 mm	91 mm
PCT50X300ET	850350	300 mm	49mm	625mm	453 mm	91 mm
PCT50X450ET	850360	450 mm	49mm	775mm	603 mm	91 mm
PCT50X500ET	850370	500 mm	49mm	852mm	653 mm	91 mm
PCT50X600ET	850380	600 mm	49mm	925mm	753 mm	91 mm



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221
Opção 1 – Apoio ao cliente
Opção 2 – Assistência
técnica

Europa

Países Baixos:
+31 800-0200135
França:
+33 800 901 793

Europa

Alemanha:
800 1890272
Outros países:
+31 13 5835404

APAC

Xangai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

