


# Wire Basket Tray PreForm Elbow 90°



The nVent CADDY Wire Basket Tray PreForm Elbow 90° is a precision-engineered solution designed to streamline cable tray installations when a directional change is needed. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Elbow 90° delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Elbow 90° significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

## CARACTERÍSTICAS

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

**Material:** Aço  
**Acabamento:** Pregalvanized; Polyurethane



## ESPECIFICAÇÕES

Table 1/2


| Número de catálogo | Cor   | Altura (H) | Largura (W) | Length (L) | Tamanho do orifício (HS) | Raio (R) |
|--------------------|-------|------------|-------------|------------|--------------------------|----------|
| WBTR902X12         |       | 50.8 mm    | 515.62 mm   | 515.62mm   | 19.05 mm                 | 94.64mm  |
| WBTR902X12BA       | Black | 50.8 mm    | 515.62 mm   | 515.62mm   | 19.05 mm                 | 94.64mm  |
| WBTR902X18         |       | 50.8 mm    | 665.734 mm  | 665.734mm  | 19.05 mm                 | 94.64mm  |
| WBTR902X18BA       | Black | 50.8 mm    | 665.734 mm  | 665.734mm  | 19.05 mm                 | 94.64mm  |
| WBTR902X24         |       | 50.8 mm    | 817.88 mm   | 817.88mm   | 19.05 mm                 | 94.64mm  |
| WBTR902X24BA       | Black | 50.8 mm    | 817.88 mm   | 817.88mm   | 19.05 mm                 | 94.64mm  |
| WBTR902X4          |       | 50.8 mm    | 317.7 mm    | 317.7mm    |                          | 94.64mm  |
| WBTR902X4BA        | Black | 50.8 mm    | 317.7 mm    | 317.7mm    |                          | 94.64mm  |
| WBTR902X6          |       | 50.8 mm    | 365.76 mm   | 365.76mm   |                          | 94.64mm  |

| Número de catálogo | Cor   | Altura (H) | Largura (W) | Length (L) | Tamanho do orifício (HS) | Raio (R) |
|--------------------|-------|------------|-------------|------------|--------------------------|----------|
| WBTR902X6BA        | Black | 50.8 mm    | 365.76 mm   | 365.76mm   |                          | 94.64mm  |
| WBTR902X8          |       | 50.8 mm    | 416.56 mm   | 416.56mm   |                          | 94.64mm  |
| WBTR902X8BA        | Black | 50.8 mm    | 416.56 mm   | 416.56mm   |                          | 94.64mm  |

Table 2/2

| Número de catálogo | Peso unitário | Certifications                                   |
|--------------------|---------------|--------------------------------------------------|
| WBTR902X12         | 1.814 kg      | cUL, UL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X12BA       | 1.814 kg      | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X18         | 3.175 kg      | CE, nVent CADDY Wire Basket Tray System, cUL, UL |
| WBTR902X18BA       | 3.175 kg      | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X24         | 4.99 kg       | cUL, UL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X24BA       | 4.99 kg       | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X4          | 0.454 kg      | UL, CE, nVent CADDY Wire Basket Tray System, cUL |
| WBTR902X4BA        | 0.454 kg      | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X6          | 0.907 kg      | CE, nVent CADDY Wire Basket Tray System, cUL, UL |
| WBTR902X6BA        | 0.907 kg      | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X8          | 0.907 kg      | UL, cUL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X8BA        | 0.907 kg      | CE, nVent CADDY Wire Basket Tray System          |

## DIAGRAMAS



## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

#### América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

#### Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

#### Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

#### APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

