

Wire Basket Tray PreForm Tee



The nVent CADDY Wire Basket Tray PreForm Tee is a precision-engineered solution designed to streamline cable tray installations when routing cabling in two or three different directions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Tee delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Tee significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

CARACTERÍSTICAS

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in two or three directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Material: Aço
Acabamento: Pregalvanized; Polyurethane



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Cor	Altura (H)	Largura (W)	Length (L)	Tamanho do orifício (HS)	Raio (R)	Peso unitário
WBTT2X12		50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64m m	2.722 kg
WBTT2X12BA	Black	50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64m m	2.722 kg
WBTT2X18		50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64m m	4.536 kg
WBTT2X18BA	Black	50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64m m	4.536 kg

Número de catálogo	Cor	Altura (H)	Largura (W)	Length (L)	Tamanho do orifício (HS)	Raio (R)	Peso unitário
WBTT2X24		50.8 mm	817.88 mm	1013.46m m	19.05 mm	94.64m m	7.257 kg
WBTT2X24BA	Black	50.8 mm	817.88 mm	1013.46m m	19.05 mm	94.64m m	7.257 kg
WBTT2X4		50.8 mm	317.5 mm	513.08m m		94.64m m	0.454 kg
WBTT2X4BA	Black	50.8 mm	317.5 mm	513.08m m		94.64m m	0.454 kg
WBTT2X6		50.8 mm	365.76 mm	561.34m m		94.64m m	1.361 kg
WBTT2X6BA	Black	50.8 mm	365.76 mm	561.34m m		94.64m m	1.361 kg
WBTT2X8		50.8 mm	416.56 mm	612.14m m		94.64m m	1.814 kg
WBTT2X8BA	Black	50.8 mm	416.56 mm	612.14m m		94.64m m	1.814 kg
WBTT6X6		152.39999999999999 8 mm					
WBTT2X4S4		50.8 mm					
WBTT4X12		101.6 mm					
WBTT4X12BA	Black	101.6 mm					
WBTT4X18		101.6 mm					
WBTT4X18BA	Black	101.6 mm					
WBTT4X24		101.6 mm					
WBTT4X24BA	Black	101.6 mm					

Table 2/2

Número de catálogo	Cor	Altura (H)	Largura (W)	Length (L)	Tamanho do orifício (HS)	Raio (R)	Peso unitário
WBTT4X4		101.6 mm					
WBTT4X4BA	Black	101.6 mm					
WBTT4X6		101.6 mm					
WBTT4X6BA	Black	101.6 mm					
WBTT6X12		152.4 mm					
WBTT6X12BA	Black	152.4 mm					
WBTT6X18		152.4 mm					
WBTT6X18BA	Black	152.4 mm					
WBTT6X24		152.4 mm					
WBTT6X24BA	Black	152.4 mm					

Número de catálogo	Cor	Altura (H)	Largura (W)	Length (L)	Tamanho do orifício (HS)	Raio (R)	Peso unitário
WBTT6X36		152.4 mm					

DIAGRAMAS

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221
 Opção 1 – Apoio ao cliente
 Opção 2 – Assistência
 técnica

Europa

Países Baixos:
 +31 800-0200135
 França:
 +33 800 901 793

Europa

Alemanha:
 800 1890272
 Outros países:
 +31 13 5835404

APAC

Xangai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500

